

COMWELD 965 SOLDERING FLUX

PRODUCT DATA SHEET



FOR USE WITH ALL COMWELD SOFT SOLDERS

SOLDERS & FLUXES

COMWELD 965 SOLDERING FLUX

- For Use with all Comweld Soft Solders.
- Used in a Liquid Form Only.
- Highest Quality Soldering Flux.

CLASSIFICATIONS:

COMWELD 965 Soldering Flux, when used in conjunction with COMWELD Soft Solders, enables excellent joints to be made on almost all metals and combinations of metals. It is a very active flux and therefore, if used on copper, brass, bronze, etc. may be diluted if required in the ratio 1 part flux to 4 parts water.

PROCEDURE:

COMWELD 965 is sold in handy squeeze-type bottles which enables the right amount of flux to be deposited when and where required.

FLUX REMOVAL:

Remove all flux residues immediately after soldering by washing with plenty of cold water. It is advisable to protect your skin from contacting this flux. If contact is made with the skin, wash under cold water as soon as possible.

IDENTIFICATION:

Pink Liquid in Black Plastic Bottles.

PACKAGING DATA:

PACK WEIGHT / TYPE	PART NO.
125 ml Bottle	321890